

# F08965-000 | FOSC-OPGW-CSEAL-B

---



FOSC® OPGW cable seal for cable types dia. 12-14 mm and central tube dia. max. 10.5 mm or 3 metal tube

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Product Type</b>	Cable sealing
<b>Product Brand</b>	FOSC®
<b>Product Series</b>	FOSC OPGW

## General Specifications

<b>Application</b>	For use with FOSC-OPGW Fiber closures
--------------------	---------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

