

# FL2-48SPNL

---



FL2000 Fiber Splice Panel, unloaded, for 48 splices, 19 in, 2RU, putty white

## Product Classification

|                              |                               |
|------------------------------|-------------------------------|
| <b>Regional Availability</b> | Latin America   North America |
| <b>Portfolio</b>             | CommScope®                    |
| <b>Product Type</b>          | Fiber splice panel            |
| <b>Product Series</b>        | FL2000                        |

## General Specifications

|                                   |                                    |
|-----------------------------------|------------------------------------|
| <b>Functionality</b>              | Splicing                           |
| <b>Cable Exit Location</b>        | Rear, left side   Rear, right side |
| <b>Color</b>                      | Putty white                        |
| <b>Growth Configuration</b>       | Unloaded                           |
| <b>Interface, front</b>           | Unloaded                           |
| <b>Rack Type</b>                  | EIA 19 in                          |
| <b>Rack Units</b>                 | 2                                  |
| <b>Shelf Movement</b>             | Hinged                             |
| <b>Splicing Capacity, maximum</b> | 48                                 |
| <b>Total Ports, quantity</b>      | 0                                  |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Height</b> | 88.9 mm   3.5 in    |
| <b>Width</b>  | 482.6 mm   19 in    |
| <b>Depth</b>  | 256.54 mm   10.1 in |

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

# FL2-48SPNL

---

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

