

# FL2-6RSTORE

---

FL2000 Fiber Storage Panel, unloaded, 5RU, 19 in, putty white

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber storage panel
<b>Product Series</b>	FL2000

## General Specifications

<b>Functionality</b>	Slack storage
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Patching Capacity, maximum</b>	0
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	5
<b>Shelf Movement</b>	Hinged
<b>Splicing Capacity, maximum</b>	0

## Dimensions

<b>Height</b>	222.25 mm   8.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	256.54 mm   10.1 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

# FL2-6RSTORE

---

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

