# FL2-C780072KN-4A00



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 72 LC/UPC, singlemode, 8RU, 19 in, putty white

### Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FL2000
General Specifications	
Functionality	Patching   Splicing
Adapter Packs Included, quantity	6
Cable Exit Location	Rear, left side   Rear, right side
Color	Putty white
Growth Configuration	Partially loaded
Interface, front	LC/UPC
Rack Type	EIA 19 in
Rack Units	8
Shelf Movement	Hinged
Splicing Capacity, maximum	144
Total Ports, quantity	144
Dimensions	
Height	355.6 mm   14 in
Width	482.6 mm   19 in
Depth	256.54 mm   10.1 in


## Ordering Tree

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 4, 2024



## FL2-C780072KN-4A00



(mass fusion)-deck

°F) °F)

<sup>3</sup> Mounting kit shipped unattached if other than standard mounting style.

Material Specifications

···		
Finish	Powder coated	
Material Type	Steel	
Optical Specifications		
Fiber Mode	Singlemode	
Environmental Specifications		
Operating Temperature	-40 °C to +70 °C (-40 °F to +158	
Storage Temperature	-40 °C to +85 °C (-40 °F to +185	
Packaging and Weights		
Included	Mounting hardware	
Packaging quantity	1	

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 4, 2024



#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 4, 2024

