# FL2-C780072PN-6A02



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 72 LC/UPC, singlemode, 8RU, 19 in, putty white

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series FL2000

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 6

 Cable Exit Location
 Rear, left side | Rear, right side

**Color** Putty white

**Growth Configuration** Partially loaded

Interface, front LC/UPC

Rack Type EIA 19 in

Rack Units 8

Shelf MovementHingedSplicing Capacity, maximum144Total Ports, quantity72

**Dimensions** 

 Height
 355.6 mm | 14 in


 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Ordering Tree



## FL2-C780072PN-6A02



#### Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$ 

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

**Included** Mounting hardware

Packaging quantity 1

COMMSC PE°

# FL2-C780072PN-6A02

### Regulatory Compliance/Certifications

-	
CHINA-ROHS	Below maximum concentration value

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Agency