

FL2-C7N0072R7-6D00

FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 72 SC/APC, singlemode, 8RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FL2000

General Specifications

Functionality	Patching Splicing
Adapter Packs Included, quantity	12
Cable Exit Location	Rear, left side Rear, right side
Color	Putty white
Growth Configuration	Fully loaded
Interface, front	SC/APC
Rack Type	EIA 23 in
Rack Units	8
Shelf Movement	Hinged
Splicing Capacity, maximum	72
Total Ports, quantity	72

Dimensions

Height	355.6 mm 14 in
Width	584.2 mm 23 in
Depth	256.54 mm 10.1 in

Ordering Tree

FL2-C7N0072R7-6D00



Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

FL2-C7N0072R7-6D00

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant/Exempted

