## FPP-12SU-180M



HELIAX® Fiber Plug and Play 6 RRU Solution that will interface with Ericsson, Nokia, Huawei or ZTE RRU's, 180M

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Outdoor junction box

Product Brand HELIAX®

General Specifications

**Application** For use with Ericsson, Nokia, Huawei or ZTE remote radio units (RRU's)

Cable Entry Location Side

Cable Entry, quantity, maximum, right 3
Cable Entry, quantity, maximum, top 3

**Color** Gray

**Mounting** Pipe, 76.2–101.6 mm (3.0–4.0 in) OD | Wall

**Dimensions** 


 Height
 406.4 mm | 16 in

 Width
 406.4 mm | 16 in

 Depth
 234.95 mm | 9.25 in

Outline Drawing





### Material Specifications

Material Type Aluminum

**Environmental Specifications** 

Environmental SpaceIndoorOutdoorQualification StandardsIEC 60529:2001, IP67

Packaging and Weights

**Included** Mounting kit

**Weight, net** 11.299 kg | 24.91 lb

Regulatory Compliance/Certifications

**COMMSCOPE®** 

# FPP-12SU-180M

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



