# FPX-1FRP08-122



FPX Fiber Optic Termination/Splice Module, 1RU, 19in, Singlemode, 12 fiber, LC/UPC Connector, putty white

#### **OBSOLETE**

This product was discontinued on: November 14, 2019

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch/splice panel

**Product Series** FPX

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 2

Body Style Symmetrical

Cable Exit Location Rear, left side | Rear, right side

ColorPutty whiteColor, frontPutty white

**Growth Configuration** Partially loaded

Interface, front LC/UPC

Patching Capacity, maximum 12

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

**Splicing Type** Heat shrink, single fiber fusion

Total Fibers, quantity 12

Total Ports, quantity 12

**Dimensions** 

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in


**COMMSCOPE®** 

# FPX-1FRP08-122

#### Depth

304.8 mm | 12 in

### Ordering Tree



### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

#### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**COMMSCOPE®** 

# FPX-1FRP08-122

## Packaging and Weights

**Included** Mounting hardware

Packaging quantity

