

# F1A-XMHM-P

Base Product



FSJ1-50A SureFlex® Jumper with interface types NEX10 Male and 4.3-10 Male, variable length

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	FSJ1-50A

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	NEX10 Male
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	A
<b>Variable Length</b>	For custom lengths, contact your local ANDREW representative

## Dimensions

<b>Nominal Size</b>	1/4 in
---------------------	--------

## Electrical Specifications

<b>3rd Order IMD</b>	-112 dBm
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.083	27.99
1700–2200 MHz	1.106	25.96
2500–2700 MHz	1.106	25.96
3400–3800 MHz	1.222	20.01

## Jumper Assembly Sample Label

# F1A-XMHM-P

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition