FAXLCUC01

Base Product



OM4 LC/UPC to Unconnectorized, 0.9mm Tight Buffer Simplex Fiber Pigtail

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber pigtail, unjacketed

Product Brand SYSTIMAX InstaPATCH® 360

Product Series FAX

Ordering Note Minimum length may vary based on cable configuration

General Specifications

Color, boot AAquaColor, connector ABlackInterface, Connector ALC/UPCJacket ColorAquaTotal Fibers, quantity1


Dimensions

Cable Assembly Length Range (m) 1 - 20
Cable Assembly Length Range (ft) 1 - 66

Ordering Tree



FAXLCUC01



Mechanical Specifications

Cable Retention Strength, maximum $1.00 \text{ lb} @ 0 \degree | 1.00 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($+14 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Environmental Space Unrated

Packaging and Weights

Packaging quantity 2

Regulatory Compliance/Certifications

Agency Classification ANATEL Compliant

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

COMMSCOPE®

FAXLCUC01

760039347 X-TB-5K-AQ-F/G - LazrSPEED® 900µm Tight Buffered Fiber

860657284

LC/UPC Connector, Multimode, Aqua

