

AGXMPMPAL

Base Product



OM4 MPO12 (Unpinned) to MPO12 (Unpinned), Fiber Trunk Cable Assembly, 96-Fiber, Method A, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications

Color, boot A	Black
Color, connector A	Aqua
Color, boot B	Black
Color, connector B	Aqua
Construction Type	Stranded
Furcation Color	Aqua
Interface, Connector A	MPO-12/UPC Female
Interface, Connector B	MPO-12/UPC Female
Jacket Color	Aqua
Polarity	Method A
Fibers per Subunit, quantity	12
Total Fibers, quantity	96

Dimensions

Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 – 999

Ordering Tree

AGXMPMPAL



Jacket Color	
M	Aqua

Breakout Length / Option	
A	33 inch breakout, no gland
B	33 inch breakout, with gland
C	33 inch breakout, with pulling grip
1	33/60 inch breakout, no gland
2	33/60 inch breakout, with gland on side A
3	33/60 inch breakout, with pulling grip and gland on side A
4	33/120 inch breakout, no gland
5	33/120 inch breakout, with gland on side A
6	33/120 inch breakout, with pulling grip and gland on side A
T	33 inch breakout, with gland on side A
U	33 inch breakout, with pulling grip and gland on side A
V	60 inch breakout, no gland
W	60 inch breakout, with pulling grip
P	120 inch breakout, no gland
Q	120 inch breakout, with pulling grip

UOM	
F	Feet
M	Meter

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

AGXMPMPAL

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

- 760051664
P-096-MP-5K-F12AQ
 - 860366210
- Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 96 fiber multi-unit with 12 fiber subunits, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color
 - MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm