


URV2P2XHF



Ultra Low Loss (ULL) OM5, MPO24 (Unpinned) to MPO24 (Pinned), 24-Fiber, Low Smoke Zero Halogen (LSZH) Patchcord

Product Classification

Regional Availability	Australia/New Zealand Europe Latin America Middle East/Africa
Portfolio	CommScope®
Product Type	Fiber array cable assembly
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications

Color, boot A	Red
Color, boot B	Red
Color, connector A	Lime green
Color, connector B	Lime green
Construction Type	Stranded
Fibers per Subunit, quantity	24
Furcation Color	Lime green
Interface, Connector A	MPO-24/UPC Female
Interface, Connector B	MPO-24/UPC Male
Jacket Color	Lime green
Polarity	Method B Enhanced (ULL)
Total Fibers, quantity	24


Dimensions

Cable Assembly Length Range (m)	3 – 999
---------------------------------	---------

URV2P2XHF

Cable Assembly Length Range (ft) 10 – 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

760235987	–	LazrSPEED® Low Smoke Zero Halogen Riser Light Duty MPO Patchcord Cable, 24 fiber
N-024-MP-5G-F36LM/D		
860634624	–	LazrSPEED® Elite MPO Female 24 Fiber Connector, lime green
860634625	–	LazrSPEED® Elite MPO Male 24 Fiber Connector, lime green