# C100-PSMSB-3M

CNT-100 CNT  $\ensuremath{\mathbb{R}}$  Jumper with interface types SMA Male and SMB Male, 3 m

### Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-100
General Specifications	
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-100
Interface, Connector A	SMA Male
Interface, Connector B	SMB Male
Specification Sheet Revision Level	А
Dimensions	
Length	3 m   9.843 ft
Nominal Size	0.100 in
VSWR/Return Loss	

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

## Jumper Assembly Sample Label

Page 1 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 8, 2022



## C100-PSMSB-3M



### Regulatory Compliance/Certifications

#### Agency

#### Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



#### Included Products

100PSBM-CR	-	SM
100PSM-CR	-	SM
CNT-100-FR	-	CN

- SMB Male (= Female pin) for CNT-100 braided cable
- SMA Male for CNT-100 braided cable
- CNT-100-FR, CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket

Page 2 of 2

