

Fiber Optic Patch Cord, Multi-fiber, Singlemode, 4 fibers, SC/UPC to SC/UPC, yellow, 24 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution cable assembly
Product Series	FPM

General Specifications

Color, boot A	Blue
Color, boot B	Blue
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	4
Connector B, quantity	4
Construction Type	Stranded
Interface, Connector A	SC/UPC
Interface, Connector B	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	4

Dimensions

Breakout Length, connector A	635 mm 25 in
Breakout Length, connector B	990.6 mm 39 in
Cord Length	24 m 78.74 ft

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.2 dB
Insertion Loss, maximum, connector B	0.2 dB
Return Loss, minimum, connector A	57 dB
Return Loss, minimum, connector B	57 dB

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

