

F1A-XMPNF-5M

FSJ1-50A SureFlex® Jumper with interface types NEX10 Male Push-Pull and N Female, 5 m



Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	NEX10 Male
Interface, Connector B	N Female
Specification Sheet Revision Level	A

Dimensions

Length	5 m 16.404 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.135	23.98
1700–2200 MHz	1.135	23.98
2500–2700 MHz	1.135	23.98
3400–3800 MHz	1.222	20.01

Jumper Assembly Sample Label

F1A-XMPNF-5M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system