L4-HMDM-8-SGW-D



D-CLASS LDF4-50A SureFlex® Jumper with interface types 4.3-10 Male and 7-16 Din Male with HELIAX® SureGuard weatherproofing, 8 ft

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port
- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® D-CLASS, dynamic PIM

Product Brand HELIAX® | SureFlex®

Product Series LDF4-50A

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector A4.3-10 MaleInterface, Connector B7-16 DIN Male

Specification Sheet Revision Level

Dimensions

Length 2.438 m | 7.999 ft

Nominal Size 1/2 in

Logo Image



L4-HMDM-8-SGW-D



Electrical Specifications

3rd Order IMD Dynamic -116 dBm

3rd Order IMD Dynamic Test MethodTwo +43 dBm carriers per IEC 62037

DTF, Connector A -34 dB

DTF, Connector B -34 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.065	30.04
1700-2200 MHz	1.065	30.04
2200-2700 MHz	1.106	25.96

Jumper Assembly Sample Label



L4-HMDM-8-SGW-D



Environmental Specifications

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system