

PTS1A-PDMDM-7

PTS1-50-HRL SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male, 7FT



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	PTS1-50-HRL

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Length	2.134 m 7.001 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.222	20.01

Jumper Assembly Sample Label

PTS1A-PDMDM-7



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition