

# F4S-HMDR-1M-P-SGW



RSJ4-50 SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Right Angle Male with HELIAX® SureGuard weatherproofing, 1 meter

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port
- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

|                       |                               |
|-----------------------|-------------------------------|
| <b>Product Type</b>   | SureFlex® Premium, static PIM |
| <b>Product Brand</b>  | HELIAX®   SureFlex®           |
| <b>Product Series</b> | RSJ4-50                       |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Right angle   |
| <b>Interface, Connector A</b>             | 4.3-10 Male   |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | A             |

## Dimensions

|                     |                |
|---------------------|----------------|
| <b>Length</b>       | 1 m   3.281 ft |
| <b>Nominal Size</b> | 1/2 in         |

## Electrical Specifications

|   |                      |
|---|----------------------|
| <b>3rd Order IMD Static</b>             | -116 dBm             |
| <b>3rd Order IMD Static Test Method</b> | Two +43 dBm carriers |
| <b>DTF, Connector A</b>                 | -34 dB               |
| <b>DTF, Connector B</b>                 | -34 dB               |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz    | 1.083 | 27.99            |
| 1700–2200 MHz  | 1.083 | 27.99            |
| 2200–2700 MHz  | 1.135 | 23.98            |

# F4S-HMDR-1M-P-SGW

## Jumper Assembly Sample Label



## Environmental Specifications

|                               |   |
|-------------------------------|---|
| <b>Immersion Test Method</b>  | Meets IEC 60529:2001, IP68 in mated condition |
| <b>Weatherproofing Method</b> | HELIAX® SureGuard weatherproofing boot        |

## Packaging and Weights

|                 |                      |
|-----------------|----------------------|
| <b>Included</b> | Weatherproofing boot |
|-----------------|----------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

|         |   |   |
|---------|---|---|
| RSJ4-50 | – | RSJ4-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket |
|---------|---|---|