

# F1B-SRQMR-10

---

FSJ1-50A SureFlex® Jumper with interface types QMA Male Right Angle and SMA Male Right Angle, 10 ft



## Product Classification

**Product Type** SureFlex® standard

**Product Series** FSJ1-50A

## General Specifications

**Body Style, Connector A** Right angle

**Body Style, Connector B** Right angle

**Interface, Connector A** QMA Male

**Interface, Connector B** SMA Male

## Dimensions

**Length** 3.048 m | 10 ft

**Nominal Size** 1/4 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.44	15

## Jumper Assembly Sample Label

# F1B-SRQMR-10

---



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Included Products

- FSJ1-50A – FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket