

F2A-PHMDR-4M

FSJ2-50 SureFlex® Jumper with interface types 4.3 -10 Male and 7-16 DIN Male Right Angle, 4 m



Product Classification

Product Type SureFlex® standard

Product Series FSJ2-50

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Right angle

Interface, Connector A 4.3-10 Male

Interface, Connector B 7-16 DIN Male

Specification Sheet Revision Level A

Dimensions

Length 4 m | 13.123 ft

Nominal Size 3/8 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.44	15

Jumper Assembly Sample Label

F2A-PHMDR-4M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

FSJ2-50	-	FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket
---------	---	---