

# F2A-PHMDR-7M

---

FSJ2-50 SureFlex® Jumper with interface types 4.3 -10 Male and 7-16 DIN Male Right Angle, 7 m



## Product Classification

**Product Type** SureFlex® standard

**Product Series** FSJ2-50

## General Specifications

**Body Style, Connector A** Straight

**Body Style, Connector B** Right angle

**Interface, Connector A** 4.3-10 Male

**Interface, Connector B** 7-16 DIN Male

**Specification Sheet Revision Level** A

## Dimensions

**Length** 7 m | 22.966 ft

**Nominal Size** 3/8 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.44	15

## Jumper Assembly Sample Label

# F2A-PHMDR-7M



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

- FSJ2-50 – FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket