

# L4-HMDM-20-SGW-D

---



D-CLASS LDF4-50A SureFlex® Jumper with interface types 4.3-10 Male and 7-16 Din Male with HELIAX® SureGuard weatherproofing, 20 ft

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port
- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

|                       |                                |
|-----------------------|--------------------------------|
| <b>Product Type</b>   | SureFlex® D-CLASS, dynamic PIM |
| <b>Product Brand</b>  | HELIAX®   SureFlex®            |
| <b>Product Series</b> | LDF4-50A                       |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Straight      |
| <b>Interface, Connector A</b>             | 4.3-10 Male   |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | A             |

## Dimensions

|                     |                 |
|---------------------|-----------------|
| <b>Length</b>       | 6.096 m   20 ft |
| <b>Nominal Size</b> | 1/2 in          |

## Logo Image

# L4-HMDM-20-SGW-D



## Electrical Specifications

|  |                                    |
|--|------------------------------------|
| <b>3rd Order IMD Dynamic</b>             | -116 dBm                           |
| <b>3rd Order IMD Dynamic Test Method</b> | Two +43 dBm carriers per IEC 62037 |
| <b>DTF, Connector A</b>                  | -34 dB                             |
| <b>DTF, Connector B</b>                  | -34 dB                             |

## VSWR/Return Loss

| <b>Frequency Band</b> | <b>VSWR</b> | <b>Return Loss (dB)</b> |
|-----------------------|-------------|-------------------------|
| <b>698–960 MHz</b>    | 1.065       | 30.04                   |
| <b>1700–2200 MHz</b>  | 1.065       | 30.04                   |
| <b>2200–2700 MHz</b>  | 1.106       | 25.96                   |

## Jumper Assembly Sample Label

# L4-HMDM-20-SGW-D



## Environmental Specifications

|                               |   |
|-------------------------------|---|
| <b>Immersion Test Method</b>  | Meets IEC 60529:2001, IP68 in mated condition |
| <b>Weatherproofing Method</b> | HELIAX® SureGuard weatherproofing boot        |

## Packaging and Weights

|                 |                      |
|-----------------|----------------------|
| <b>Included</b> | Weatherproofing boot |
|-----------------|----------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

