

Outdoor Distribution boxes

The Outdoor Distribution boxes 20, 50 and 100 pairs serve as a connection and branching box for outdoor use. They accommodate LSA-PLUS® Series 2 backmount frame modules, with or without overvoltage protection.

The Outdoor Distribution Box up to 200 Pairs is designed to serve not only as a terminating distribution box but also as a connection and branching box both for outdoor use. It can accommodate LSA-PLUS® series 2 connection, disconnection or switching modules, with or without overvoltage protection.

Features and benefits

- Housing with hinged cover
 - o Opening approximately 110° for 20, 50 and 100 pairs Outdoor box
 - o Opening approximately 180° for 200 pairs Outdoor box
- Space for owner's label on the cover (approximately 24 mm x 100 mm)
- Space for additional label on the cover
- Backmount frame from 2 up to 20 pcs LSA-PLUS® 10-pair modules
- Earth wire up to Ø 4 mm (for 20 and 50 pair) or Ø 2,5 mm² (for 100 and 200 pair) possible
- Sheath grounding clamp
- Locking optional: plumbing or locking

Specifications

Design and configurations

Product description	Size (mm) Height x depth x width	Cable entry	Space for additional label on cover	Number of modules
Outdoor Distribution box 20 pairs	H173 x D87 x W137	2 for cable up to Ø 15 mm 3 for cable up to Ø 2 mm 1 for cable up to Ø 9 mm (for earth connection)	65x100mm	2x LSA- PLUS® 10-pair modules
Outdoor Distribution box 50 pairs	H210 x D108 x W191	1 for cable up to Ø 23 mm 2 for cable up to Ø 32 mm 4 for cable up to Ø 14, 7 mm 1 for cable up to Ø 9 mm (for earth connection)	125x100mm	5x LSA- PLUS® 10-pair modules
Outdoor Distribution box 100 pairs	H390 x D124 x W223	3 for cable up to Ø 32 mm 4 for cable up to Ø 23 mm 1 for cable up to Ø 9 mm (for earth connection)	300x110mm	10x LSA- PLUS® 10-pair modules



Outdoor distribution boxes


Outdoor Distribution box	H238 x D125 x W640	2 for cable up to Ø35 mm (Pg 36)	20x LSA- PLUS®
200 pairs		1 for cable up to Ø 23 mm	10-pair modules
·		3 for cable up to Ø 18 mm	·
		4 for cable up to Ø 13 mm	
		1 for cable up to Ø 7 mm	
		(for earth connection)	




Outdoor Distribution box – 20 pairs (shown with IDC modules, ordered separately)



Outdoor Distribution box – 50 pairs (shown with IDC modules, ordered separately)



Dimensions, in mm



Dimensions, in mm




Outdoor distribution boxes




Outdoor Distribution box – 100 pairs (shown with IDC modules, ordered separately)



Outdoor Distribution box – 200 pairs (picture is not equal to the shipment)



Dimensions, in mm



Dimensions in mm



General attributes & mechanical characteristics

Installation:

- Prepared for mounting on wall or pole (wood, metal or concrete)
- No additional pole mounting kit necessary for Outdoor Distribution boxes 20, 50 and 100 pairs.
- For Outdoor Distribution box 200 pairs: mounting material for metal or concrete poles needed

Product specifications:

Material

Housing: 20 pairs ABS, black

50 pairs PC/ABS, UV-stabilized, UL 94 V-0, grey

100 pairs ASA, UV-stabilized, UL 94 V-0, grey

200 pairs glass-fiber reinforced polyester HUP 19/23, grey

Cover: Fiberglass reinforced polyester HUP 19/23, grey

Screws (for cover): Polyamide UV-stabilized (for 50 and 100 pairs), brass, tin-plated (for 200 pairs only)

Stuffing boxes: brass, tin-plated (for 200 pairs only)

Grommets: Synthetic rubber, black (not for 20 pair), polyethylene, black

Backmount frame: Stainless steel Screws: Stainless steel

Earthing: Brass, nickel plated and stainless steel

Protection class: For 20, 50 and 100 pairs IP 54 (optional IP 64 with sealing), for 200 pairs IP 64 (with sealing)

Distribution Outdoor boxes

Order number	Product description	
70831301-00	Outdoor Distribution box for LSA-PLUS®	
	Series 2 modules (up to 20 lines) with backmount frame	
70831401-00	Outdoor Distribution box for LSA-PLUS®	
	Series 2 modules (up to 50 lines) with backmount frame	
70831501-00	Outdoor Distribution box for LSA-PLUS®	
	Series 2 modules (up to 100 lines) with backmount frame	
70831200-00	Outdoor Distribution box up to 200 pairs without connection modules	

Distribution Outdoor boxes 20, 50 and 100 pairs - Accessories

Order number	Product description
OEC-70831900-01	Lock for 20 line Outdoor Distribution box
OEC-70831901-01	Lock for 50 or 100 line Outdoor Distribution box
70831902-02	Sealing for 20, 50 and 100 line Outdoor Distribution box*

^{*} Sealing gasket kit - cut to length per box size

Distribution Outdoor boxes 200 pairs - Accessories

Order number	Product description
60343084-01	Shielding contact lead 170 mm
70831291-00	Add on kit lock*
70831290-00	Pole and wall fixing kit

^{*} Lock kit for 200pair box on request.





commscope.com

Visit our website or contact your local CommScope representative for more information. © 2019 CommScope, Inc. All rights reserved.

All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability with a number of CommScope's facilities across the globe certified in accordance with international standards including ISO 9001, TL 9000, and ISO 14001. Further information regarding CommScope's commitment can be found at www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability. PA-113095-EN (03/19)