



Fiber Optic Pigtail, Simplex, Singlemode, LSH/APC to Stub, 0.9 mm diameter, 3 m

## OBSOLETE

This product was discontinued on: June 6, 2019

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber pigtail, jacketed
<b>Product Series</b>	OCP

## General Specifications

<b>Connector A, quantity</b>	1
<b>Color, boot A</b>	Green
<b>Color, connector A</b>	Green
<b>Interface, Connector A</b>	LSH/APC
<b>Jacket Color</b>	Yellow
<b>Total Fibers, quantity</b>	1

## Dimensions

<b>Cord Length</b>	3 m   9.843 ft
--------------------	----------------

## Ordering Tree

# CC1164-000 | OCP-E9-03MASEN-XX



Connector/adaptor type		
Standard C grade	Superior B grade	Type
S1	SF	SC/UPC
S2	SG	SC/APC 8°
S3	SH	SC/APC 9°
L1	LF	LC/UPC
L2	LG	LC/APC
-	EC	LSH/APC 8°

Cable type			Fiber type
ASEN	900 µm	Semi-tight jacket	A1
HSEN	900 µm	Semi-tight jacket	A2

Cable length	
02	2 meters

- Standard Configuration by default 900µm buffer  
 buffer color : yellow  
 250 µm color : natural or milky white

## Optical Specifications

**Fiber Mode** Singlemode  
**Fiber Type** G.657.A1, TeraSPEED®

## Environmental Specifications

**Environmental Space** Low Smoke Zero Halogen (LSZH)

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

