


CC2247-000 | OCP-L1-06MASIA-XX



Fiber Optic Pigtail, Simplex, Singlemode, LC/UPC to Stub, yellow, 6 m

Product Classification

Regional Availability	EMEA
Product Type	Fiber pigtail, jacketed
Product Series	OCP

General Specifications

Connector A, quantity	1
Color, boot A	Blue
Color, connector A	Blue
Interface, Connector A	LC/UPC
Jacket Color	Yellow
Total Fibers, quantity	1

Dimensions

Cord Length	6 m 19.685 ft
--------------------	-----------------

Ordering Tree



Connector/adaptor type		
Standard C grade	Superior B grade	Type
S1	SF	SC/UPC
S2	SG	SC/APC 8°
S3	SH	SC/APC 9°
L1	LF	LC/UPC
L2	LG	LC/APC
-	EC	LSH/APC 8°

- Standard Configuration by default for 1.8mm
 Jacket color : Yellow
 buffer color : milky white or transparent
 250 µm color : natural or milky white

Cable type			Fiber type
ASIA	1.8 mm simplex	LSZH jacket	A1
HSIA	1.8 mm simplex	LSZH jacket	A2

Cable length	
06	6 meters
20	20 meters

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1, TeraSPEED®

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

