

760230102 | 360-imV-CNTRLR-AR



SYSTIMAX 360™ imVision® Controller

OBSOLETE

This product was discontinued on: January 31, 2019

Replaced By:

760237877

imV-CNTRLR-X-AR

imVision Controller X (Argentina Only)

Product Classification

Regional Availability	Latin America
Portfolio	SYSTIMAX®
Product Type	Controller unit
Product Brand	iPatch® imVision®

General Specifications

Color	Cool gray
--------------	-----------

Dimensions

Height	81.28 mm 3.2 in
Width	19 mm 0.748 in
Depth	211.33 mm 8.32 in

Electrical Specifications

Input Voltage	100–240 Vac
Output Current at Voltage, continuous	1.25 A @ 12 Vdc
Power Frequency	50–60 Hz

Material Specifications

760230102 | 360-imV-CNTRLR-AR

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate | Steel

Environmental Specifications

Operating Temperature 0 °C to +50 °C (+32 °F to +122 °F)
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity Up to 95%, non-condensing
Flammability Rating UL 94 V-0
Safety Standard C-tick | CE | GOST | KC | cUL

Packaging and Weights

Included 16 in panel bus jumper | 7 ft patch cord | Forty-four position bus panel | Power supply, 1.25A @ 12 Vdc output, 100-240 Vac 50-60 Hz input
Packaging quantity 1
Weight, net 1.288 kg | 2.84 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

