

7663065-0008 | ION-U H 18P/21P/26-Vac-M2



ION-U® High Power Remote Unit for DCS 1800, IMT 2100 and IMT 2600 Band Applications

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Product Type	Remote unit
Product Brand	ION-U®

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	High

Electrical Specifications

Impedance	50 ohm
License Band	DCS 1800 IMT 2100 IMT 2600
Voltage Range	100 to 240 Vac

Electrical Specifications, Rx (Uplink)

Operating Frequency Band	1710 – 1785 MHz (DCS 1800) 1920 – 1980 MHz (IMT 2100) 2500 – 2570 MHz (IMT 2600)
Wavelength	1310 nm 1550 nm

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	1805 – 1880 MHz (DCS 1800) 2110 – 2170 MHz (IMT 2100) 2620 – 2690 MHz (IMT 2600)
---------------------------------	--

Output Power per Antenna Port

Note	* 66 dBc @ 2 and 4 carriers 63 dBc @ 8 carriers 60 dBc @ 16 carriers ** For carrier bandwidth < 5 MHz output power shall be reduced by 2 dB
-------------	---

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Above maximum concentration value

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

