

7663065-0010 | ION-U H 21P/26-Vac-M2



ION-U® High Power Remote Unit for IMT 2100 and IMT 2600 Band Applications

OBSOLETE

Product Classification

Product Type Remote unit
Product Brand ION-U®

General Specifications

Note Detailed Product Specifications are available. Please contact your local CommScope representative.

Power Class High

Electrical Specifications

Impedance 50 ohm
License Band IMT 2100 | IMT 2600
Voltage Range 100 to 240 Vac

Electrical Specifications, Rx (Uplink)

Operating Frequency Band 1920 – 1980 MHz (IMT 2100) | 2500 – 2570 MHz (IMT 2600)
Wavelength 1310 nm | 1550 nm

Electrical Specifications, Tx (Downlink)

Operating Frequency Band 2110 – 2170 MHz (IMT 2100) | 2620 – 2690 MHz (IMT 2600)

Output Power per Antenna Port

Note ** For carrier bandwidth < 5 MHz output power shall be reduced by 2 dB