

1918388-3

Fiber Optic Connector Kit, LC, XG, 900 µm, duplex

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA North America
Portfolio	NETCONNECT®
Product Type	Fiber connector

General Specifications

Application	For use with buffered fiber
Body Style	Duplex
Boot Style	Short
Color	Aqua
Color, boot	Aqua
Interface	LC/UPC

Dimensions

Compatible Cable Diameter	0.9 mm 0.035 in
----------------------------------	-------------------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM3 OM4

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

1918388-3

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

