



PICABOND® Connector, 250 loose piece, 400 Vdc, pink

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for high count straight splicing applications

OBSOLETE

This product was discontinued on: March 15, 2020

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Splice
Product Brand	PICABOND®
Product Series	PICABOND

General Specifications

Connector Color Code	Green/Amber
Connector Sealant	Unfilled
Connector Splicing Type	High Count Straight

Dimensions

Compatible Conductor Gauge, solid	28–24 AWG
--	-----------

Electrical Specifications

Safety Voltage Rating	400 Vdc
------------------------------	---------

Material Specifications

Contact Base Material	Phosphor Bronze
Contact Plating Material	Tin
Insulation Material	Air Core PIC Paper or Pulp

Environmental Specifications

552466-4

Operating Temperature -40 °C to +60 °C (-40 °F to +140 °F)

Environmental Space Outdoor

Packaging and Weights

Packaging quantity 250

Packaging Type Loose piece