

Remote Units US							
Classification	Region	ID	Description	Life Cycle Status	Minimum MU SW Package	Latest Supported Version	Replacement
Remote Unit	US	7669582-0001	ION-U L 7/80-85/17P/19P-Vac	Available	1.64	1.97	7669582-0007
Remote Unit	US	7669582-0002	ION-U L 7/80-85/17P/19P-Vdc	Available	1.64	1.97	7669582-0008
Remote Unit	US	7669582-0003	ION-U L 7/80-85/17P/19P-Vdc/100	Available	1.64	1.97	7669582-0009
Remote Unit	US	7669582-0004	ION-U L 7/80-85/17P/19P-Vac-ap	Not Available			
Remote Unit	US	7669582-0005	ION-U L 7/80-85/17P/19P-Vdc-ap	Not Available			
Remote Unit	US	7669582-0006	ION-U L 7/80-85/17P/19P-Vdc/100-ap	Not Available			
Remote Unit	US	7669582-0007	ION-U L 7/80-85/17EP/19P-Vac	Available soon	1.75	1.97	
Remote Unit	US	7669582-0008	ION-U L 7/80-85/17EP/19P-Vdc	Available soon	1.75	1.97	
Remote Unit	US	7669582-0009	ION-U L 7/80-85/17EP/19P-Vdc/100	Available soon	1.75	1.97	
Remote Unit	US	7699392-0001	ION-U EU L 23/23-Vac	Available soon	1.75	1.97	
Remote Unit	US	7699392-0002	ION-U EU L 23/23-Vdc	Available soon	1.75	1.97	
Remote Unit	US	7698400-0001	ION-U H 7P/80-85P/17P/19P -Vac-M2	Available	1.69	1.97	7698400-0003
Remote Unit	US	7698400-0002	ION-U H 7P/80-85P/17P/19P -Vdc-M2	Available	1.69	1.97	7698400-0004
Remote Unit	US	7698400-0003	ION-U H 7P/80-85P/17EP/19P -Vac-M2	Available	1.75	1.97	
Remote Unit	US	7698400-0004	ION-U H 7P/80-85P/17EP/19P -Vdc-M2	Available	1.75	1.97	
Remote Unit	US	7698401-0001	ION-U EU H 7P/80-85P/17P/19P -Vac-M2	Available	1.75	1.97	7698401-0003
Remote Unit	US	7698401-0002	ION-U EU H 7P/80-85P/17P/19P -Vdc-M2	Available	1.75	1.97	7698401-0004
Remote Unit	US	7698401-0003	ION-U EU H 7P/80-85P/17EP/19P -Vac-M2	Available	1.75	1.97	
Remote Unit	US	7698401-0004	ION-U EU H 7P/80-85P/17EP/19P -Vdc-M2	Available	1.75	1.97	
Remote Unit	US	7698403-0001	ION-U EU H 23/23 -Vdc-M2	Available soon	1.90	1.97	
Remote Unit	US	7698403-0002	ION-U EU H 23/23 -Vac-M2	Available soon	1.90	1.97	
Remote Unit	US	7674471-0001	ION-U H 17P2 Vac-M	Available	1.64	1.97	
Remote Unit	US	7674433-0001	ION-U EU H 19P2 Vac-M	Available	1.64	1.97	
Remote Unit	US	7674471-0002	ION-U H 17P2 Vac-M-SV	Available	1.64	1.97	
Remote Unit	US	7674433-0002	ION-U EU H 19P2-Vac -M-SV	Available	1.64	1.97	
Remote Unit	US	7769134-0001	ION-U EU L 17EP/17EP-Vac	Available	1.96	1.97	
Remote Unit	US	7769134-0002	ION-U EU L 17EP/17EP-Vdc/100	Available	1.96	1.97	
Remote Unit	US	7776915-0002	ION-U EU L 25/25 TDD Vac	Available	1.96	1.97	
Remote Unit	US	7776915-0004	ION-U EU L 25/25 TDD Vdc	Available	1.96	1.97	

Remote Units EMEA/APAC							
Classification	Region	ID	Description	Life Cycle Status	Minimum MU SW Package	Latest Supported Version	Replacement
Remote Unit	EMEA/APAC	7663274-0001	ION-U L 9/18/21/26-Vac	Available	1.64	1.97	
Remote Unit	EMEA/APAC	7663274-0002	ION-U L 9/18/21/26-Vdc	Available	1.64	1.97	
Remote Unit	EMEA/APAC	7663274-0003	ION-U L 18/26-Vac	Available	1.69	1.97	
Remote Unit	EMEA/APAC	7663274-0004	ION-U L 18/26-Vdc	Available	1.69	1.97	
Remote Unit	EMEA/APAC	7715812-0001	ION-U EU L 8/8/18/26-Vac	Available	1.80	1.97	
Remote Unit	EMEA/APAC	7663065-0001	ION-U H 9/18P/21P/26 -Vac-M2	Obsolete	1.69	1.97	7663065-0007
Remote Unit	EMEA/APAC	7663065-0002	ION-U H 9/18P/21P/26 -Vdc-M2	Obsolete	1.69	1.97	No successor
Remote Unit	EMEA/APAC	7663065-0003	ION-U H 18P/26 -Vac-M2	Obsolete*	1.69	1.97	No successor
Remote Unit	EMEA/APAC	7663065-0004	ION-U H 18P/26 -Vdc-M2	Obsolete	1.69	1.97	No successor
Remote Unit	EMEA/APAC	7663065-0005	ION-U H 21P/26-Vac-M2	Obsolete	1.69	1.97	
Remote Unit	EMEA/APAC	7663065-0006	ION-U H 18P/21P -Vac-M2	Obsolete	1.69	1.97	No successor
Remote Unit	EMEA/APAC	7663065-0007	ION-U H 9/18P/21P/26 -Vac-M2	Available	1.70	1.97	
Remote Unit	EMEA/APAC	7663065-0008	ION-U H 18P/21P/26 -Vac-M2	Available	1.70	1.97	
Remote Unit	EMEA/APAC	7663065-0009	ION-U H 9/18P/21P -Vac-M2	Available	1.70	1.97	
Remote Unit	EMEA/APAC	7663065-0010	ION-U H 21P/26-Vac-M2	Available	1.70	1.97	
Remote Unit	EMEA/APAC	7714558-0001	ION-U H 8/9/18P/21P-Vac-M2	Available	1.75	1.97	
Remote Unit	EMEA/APAC	7681488-0001	ION-U EU H 8/8/18P/26 -Vac-M2	Obsolete	1.69	1.97	7681488-0008
Remote Unit	EMEA/APAC	7681488-0002	ION-U EU H 8/8/18P/26 -Vdc-M2	Obsolete	1.69	1.97	No successor
Remote Unit	EMEA/APAC	7681488-0003	ION-U EU H 18P/26 -Vac-M2	Obsolete	1.69	1.97	7681488-0006
Remote Unit	EMEA/APAC	7681488-0004	ION-U EU H 8/8/26 -Vac-M2	Obsolete	1.69	1.97	No successor
Remote Unit	EMEA/APAC	7681488-0005	ION-U EU H 26 -Vac-M2	Obsolete	1.69	1.97	No successor
Remote Unit	EMEA/APAC	7681488-0006	ION-U EU H 18P/26 -Vac-M2	Available	1.70	1.97	
Remote Unit	EMEA/APAC	7681488-0007	ION-U EU H 8 -Vac-M2	Available	1.70	1.97	
Remote Unit	EMEA/APAC	7681488-0008	ION-U EU H 8/8/18P/26 -Vac-M2	Available	1.70	1.97	
Remote Unit	EMEA/APAC	7699392-0001	ION-U EU L 23/23 Vac	Available	1.75	1.97	
Remote Unit	EMEA/APAC	7699392-0002	ION-U EU L 23/23 VDC/100	Available	1.75	1.97	
Remote Unit	EMEA/APAC	7663274-0005	ION-U L 18/21-Vac (N)	Available	1.69	1.97	
Remote Unit	EMEA/APAC	7663274-0011	ION-U L 18/21-Vac	Available	1.69	1.97	
Remote Unit	EMEA/APAC	7663274-0012	ION-U L 18/21-Vdc	Available	1.69	1.97	
Remote Unit	EMEA/APAC	7715812-0002	ION-U EU L 8/8/18/26-Vdc	Available	1.80	1.97	
Remote Unit	EMEA/APAC	7715812-0003	ION-U EU L 8-Vac	Available	1.80	1.97	
Remote Unit	EMEA/APAC	7663274-0101	ION-U L 18/21/26-Vac	Available	1.90	1.97	
Remote Unit	EMEA/APAC	7663274-0011	ION-U H 18P/21P -Vac-M2	Available	1.90	1.97	
Remote Unit	EMEA/APAC	7775884-0001	ION-U EU H 18P/21P/26-Vac-M2	Available	1.95.1	1.97	
Remote Unit	EMEA/APAC	7663274-0107	ION-U L 18/21/26-Vac (4.3-10)	Available	1.95.1	1.97	
Remote Unit	EMEA/APAC	7812729-0001	ION-U EU H 7-8-Vac-M2	Available	1.96	1.97	
Remote Unit	EMEA/APAC	7775884-0002	ION-U EU H 18P/21P -Vac-M2	Available	1.96	1.97	

Master Unit								
Classification	Region	ID	Description	Material Status	Minimum SW Requirements	Upgrade Required	Latest Supported Version	Replacement
Master Unit	All	7669580-00	OTRX L/4	Available	1.63		1.97	
Master Unit	All	7769958-00	OTRX L/2	Available	1.95.1		1.97	
Master Unit	All	7645469-01	OTRX H	Obsolete	1.69		1.97	
		7645469-02	OTRX H1	Available				
		7645469-03	OTRX H1	Available				
Master Unit	EMEA/APAC	7645470-01	OTRX H/F	Available	1.69		1.97	
		7645470-02						
		7645470-03						
Master Unit	US	7674265-00	OTRX H M1	Available	1.64		1.97	
Master Unit	US	7698434-00	OTRX H1/F1	Available	1.69		1.97	
		7698434-01						
Master Unit	All	7697088-00	SPL-O/2	Available	1.69		1.97	
Master Unit	All	7697120-00	SPL-O/4	Available	1.69		1.97	
Master Unit	All	7658884-01	SMX 8x4	Available	1.64		1.97	
Master Unit	All	7657752-00	ZC 8x8	Available	1.64		1.97	
Master Unit	All	7676650-00	ZC 2x2	Available	1.64		1.97	
Master Unit	All	7699985-00	SC 8x8	Available	1.70		1.97	
Master Unit	All	7658895-00	dSMR	Obsolete	1.64		1.97	
		7658895-01		Available	1.80			
Master Unit	All	7645407-00	SRC	Obsolete	1.64		1.97	7645406-01
Master Unit	All	7645407-01	SRC	Available	1.64		1.97	
Master Unit	All	7645406-00	IFC	Available	1.64		1.97	
Master Unit	All	7641375-01	IFC-S	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634506-02	i-POI 26/26	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634533-01	i-POI 21-G	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634531-01	i-POI 21-U	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634530-01	i-POI 18/18	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634529-01	i-POI 18-U	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634528-01	i-POI 18-G	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634527-01	i-POI 9-U	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634526-01	i-POI 9-G	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634525-01	i-POI 8/8	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634517-01	i-POI 90-U	Available	1.64		1.97	
Master Unit	EMEA/APAC	7634516-01	i-POI 80-U	Available	1.64		1.97	
Master Unit	US	7634513-01	i-POI 7/7	Available	1.64		1.97	
Master Unit	US	7634512-01	i-POI 17/17	Obsolete	1.64		1.97	7712241-00
Master Unit	US	7634511-01	i-POI 17-U	Obsolete	1.64		1.97	7712241-00
Master Unit	US	7634510-01	i-POI 85-U	Available	1.64		1.97	
Master Unit	US	7634509-02	i-POI 85-G	Available	1.64		1.97	
Master Unit	US	7634508-02	i-POI 19-U	Available	1.64		1.97	
Master Unit	US	7634507-01	i-POI 19-G	Available	1.64		1.97	
Master Unit	US	7677897-00	i-POI L M1	Available	1.64		1.97	
Master Unit	US	7634537-00	i-POI 19/19	Available	1.64		1.97	
		7634537-01						
Master Unit	US	7634540-00	i-POI 85/85	Available	1.67		1.97	
Master Unit	EMEA/APAC	7634538-00	i-POI 9/9	Available	1.67		1.97	
Master Unit	EMEA/APAC	7634539-00	i-POI 21/21	Available	1.67		1.97	
Master Unit	EMEA/APAC	7699551-00	i-POI L 8/4	Available	1.67		1.97	
Master Unit	EMEA/APAC	7699552-00	i-POI L 18/4	Available	1.67		1.97	
Master Unit	EMEA/APAC	7699553-00	i-POI L 21/4	Available	1.67		1.97	

Master Unit								
Classification	Region	ID	Description	Material Status	Minimum SW Requirements	Upgrade Required	Latest Supported Version	Replacement
Master Unit	EMEA/APAC	7699554-00	i-POI L 9/4	Available	1.67		1.97	
Master Unit	EMEA/APAC	7699555-00	i-POI L 26/4	Available	1.67		1.97	
Master Unit	US	7634543-00	i-POI 23/23	Available	1.75		1.97	
Master Unit	US	7712241-00	i-POI 17E/17E	Available	1.75		1.97	
Master Unit	US	7707724-00	i-POI L 7L/2	Available	1.75		1.97	
Master Unit	US	7707725-00	i-POI L 7U/2	Available	1.75		1.97	
Master Unit	US	7707726-00	i-POI L 85/2	Available	1.75		1.97	
Master Unit	US	7707729-00	i-POI L 17E/2	Available	1.75		1.97	
Master Unit	US	7707730-00	i-POI L 19/2	Available	1.75		1.97	
Master Unit	US	7707731-00	i-POI L 23/2	Available	1.75		1.97	
Master Unit	US	7715671-01	I-POI 25/25 TDD	Available	1.75		1.97	
Master Unit	US	7684520-00	i-POI 7AL/7AL	Available	1.75		1.97	
Master Unit	All	7627572-0012	RMC1600	Available	V1.64		1.97	
Master Unit	All	7724875-0001	RMC1900	Available	V1.96		1.97	
Master Unit	All	7678972-00	ESC 8	Available	V1.64		1.97	
Master Unit	All	7161351-01	Display & Keyboard Drawer, 1HU, 12V	Available	V1.64		1.97	
Master Unit	All	7698415-00	CM/MRL	Available soon	-		1.97	
Master Unit	All	7694117-00	CM/MC88i	Obsoleete	-		1.97	No successor
Master Unit	All	7694118-00	CA	Available	1.70		1.97	
Master Unit	All	7640681-00	PDU 30	Obsolete	1.64		1.97	7640681-01
Master Unit	All	7640681-01	PDU 30	Available	1.64		1.97	
Master Unit	All	7641606-01	PF850	Available	Not Applicable		Not Applicable	
Master Unit	All	7670265-00	BM	Available	Not Applicable		Not Applicable	
Master Unit	All	7672755-00	POIF	Available	Not Applicable		Not Applicable	
Master Unit	All	7643288-01	SR 8/POI	Available	V1.66		1.97	
Master Unit	All	7644783-00 7644783-01 7644783-02	SR 12	Available	V1.69		1.97	
Master Unit	All	7659271-00 7659271-01 7659271-02	SR 12/dM	Available	V1.66 V1.69 V1.69		1.97	
Master Unit	All	7641375-00 7641375-01	IFC-S	Available	V1.66 V1.69		1.97	
Master Unit	All	7645406-00	IFC	Available	V1.66		1.97	



Contacting CommScope

CMS GLOBAL TECHNICAL SUPPORT

For additional information, please contact the CommScope Mobility Solutions (CMS) Technical Support team. Support is available 7 days a week, 24 hours a day.

Telephone Helplines: Call one of the Telephone Helpline numbers listed below to get live support, 24 hours a day.

24X7

+1 888-297-6433 (Toll free for U.S. and Canada)

EMEA 8:00-17:00 (UTC +1)

+ 800 73732837 (Toll free for parts of EMEA and Australia)

+ 49 909969333 (Toll charge incurred)

Calls to an EMEA Helpline outside of the 8:00 to 17:00 time frame will be forwarded to the 24x7 Helpline.

Online Support: To go to the CommScope Wireless Support Request web site from which you can initiate a Technical Support ticket, do one of the following:

- Scan the QR Code to the right.
- If viewing this document online as a PDF, click on the following URL link:
<http://www.commscope.com/wisupport>
- Enter the preceding URL into your web browser, and then press ENTER on your keyboard.

