FD3-AB096J00RKBM3



Enhanced Mini FDH, 96F loaded pole/wall mounted cabinet, SC/APC, PNP splitter capable, using a 100ft 1x96F Indoor OFNR Ribbon distribution cable assembly and Loose Tube pigtails capable of splicing a 36F feeder

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeIndoor - RibbonColorPutty white

Distribution Cables, quantity 1

Distribution Ports, quantity 96

Fibers per Distribution Cable, quantity 96

Fibers per Feeder Cable, quantity 36

Interface Feature, Input APC

Mounting Pole | Wall

Splitter Slots, quantity 8

Dimensions

Interface, Input

 Height
 584.2 mm | 23 in

 Width
 330.2 mm | 13 in

 Depth
 203.2 mm | 8 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Mini

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSCOPE®

SC

FD3-AB096J00RKBM3

Environmental Specifications

Environmental Space Above ground | Aerial

Qualification Standards Telcordia GR-3123-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

