

LS2-XMNM-W1-D

D-CLASS LSF2-50 SureFlex® Jumper with interface types NEX10 Male and N Male with HELIAX® SureGuard weatherproofing on NEX10 side



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	LSF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	NEX10 Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Nominal Size	3/8 in
---------------------	--------

Electrical Specifications

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037

Logo Image

LS2-XMNM-W1-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–970 MHz	1.065	30
1700–2200 MHz	1.065	30
2200–2700 MHz	1.083	28
3400–3800 MHz	1.222	20
4000–6000 MHz	1.222	20

Jumper Assembly Sample Label

LS2-XMNM-W1-D



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition