

# QUFB-48FDLCMSMHR-2

---

Q3000 Fiber Termination Blade (Module), 48 ports, LC/UPC to MPO, Singlemode, Pack of 2 blades

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber modules in blade
<b>Product Series</b>	Q3000

## General Specifications

<b>Functionality</b>	Breakout
<b>Application</b>	For use with Q3000 panels
<b>Body Style</b>	Duplex   Straight orientation
<b>Color, front</b>	Black
<b>Color, housing</b>	Black
<b>Color, rear</b>	Black
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Standard
<b>Total Ports, quantity, front</b>	48

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2

## Packaging and Weights

<b>Packaging quantity</b>	2
<b>Packaging Type</b>	Bag   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

# QUFB-48FDLCMSMHR-2

---

ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

