

760248405 | CHD08-DM-PBLC-LS-B-ULL



CHD ULL Multimode, MPO-8 distribution module, 8LC to 1x8f MPO unpinned with port blockers, dust plugs

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX ULL
Product Series	CHD

General Specifications

Functionality	Breakout
Color, front	Aqua
Color, rear	Gray
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up/up MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Shuttered	No
Total Fibers, quantity	8

Dimensions

Height	12.45 mm 0.49 in
Width	83.82 mm 3.3 in
Depth	131.83 mm 5.19 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED® 550
Insertion Loss, maximum	0.35 dB

760248405 | CHD08-DM-PBLC-LS-B-ULL

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.082 kg | 0.18 lb