

NOVUX™ CSC100 Compact Fiber Closure, splice only, no adapters, no splitters, mounting clips, 2 ID plates, 7 Dual CTU, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

This product will be discontinued on: August 3, 2023

Replaced By:

CSC3-M5A1A1BB001 NOVUX™ CSC100 Compact Fiber Closure, splice only, no adapters, no splitters, mounting clips, 2 ID

plates, 7 Dual CTU, black

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Single-ended, rectangular fiber closure

Product Brand NOVUX™
Product Series CSC 100

General Specifications

Cable Ports Quantity, total3 round ports + 6 multi-out ports (12 cables)

Cable Sealing TypeCompressed gelClosure Sealing TypeHinged with latch

Closure Style Single-ended

Color Black

Mounting Pole | Wall
Port Type No adapter

Port, quantity 0

COMMSCOPE®

Splitter Type No splitter

Splitter, quantity 0

Dimensions


 Height
 284 mm | 11.181 in

 Width
 117 mm | 4.606 in


 Depth
 77 mm | 3.031 in



Dimension Drawing








Port Configuration

Position	Cable diameter	
	mm	Inches
Feeder cable	≤14	≤ 0.55
Branch cable	≤12	≤ 0.47
Single drops	≤ 8 (flat cable: 8 x 4,5)	≤ 0.32 (flat cable: 0.32 x 0.18)
Dual drops	≤ 6,2	≤ 0.25

Ordering Tree



Environmental Specifications

Environmental Space Outdoor

UV Resistance UV stabilized

Packaging and Weights

Included Mounting hardware

Packaging quantity

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
TL 9000:2016 (R6)	Compliant to this quality management practice
UK-ROHS	Compliant







Page 5 of 5

