FPX-2FSJ/04AU016



FPX Fiber Optic Termination Panel with IFC Stranded Cable, 2RU, 19in, Singlemode, 48 fiber, SC/APC connectors, Stub tail at far end, putty white, 16m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with OSP cable

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity 4

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type OSP

Color Putty white

Color, front Putty white

Growth Configuration Fully loaded

Interface, front SC/APC

Interface, rear Stub tail

Patching Capacity, maximum 48

Rack Type EIA 19 in | EIA 23 in

Rack Units 2

Shelf Movement Sliding

Total Fibers, quantity 48

Total Ports, quantity 48

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in


COMMSCOPE®

FPX-2FSJ/04AU016

Cable Length

16 m | 52.493 ft

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

COMMSCOPE®

FPX-2FSJ/04AU016

Storage Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

