

LSX-77/OZC100

LSX Fiber Term Panel 4 Ru, 96 - SC/UPC, Singlemode IFC Stranded, 100 Meters, Far end connection Stub

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with IFC cable
Product Series	LGX

General Specifications

Functionality	Patching
Application	Used in LSX-style frames only
Cable Exit Location	Upward
Cable Stub Type	IFC, stranded
Color	Putty white
Color, front	White
Growth Configuration	Fully loaded
Interface, front	SC/UPC
Interface, rear	Stub tail
Rack Type	EIA 19 in EIA 23 in
Rack Units	4
Shelf Movement	Fixed
Total Ports, quantity	96

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in
Cable Length	100 m 328.084 ft

Material Specifications

Finish	Powder coated
Material Type	Steel

LSX-77/OZC100

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

