

LSX-LL/0WB075



LSX Fiber Term Panel 8 Ru, 288 - SC/APC, Singlemode IFC Stranded, 75 Meters, Far end connection Stub

Product Classification

| | |
|------------------------------|-----------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel, with IFC cable |
| Product Series | LGX |

General Specifications

| | |
|------------------------------|-------------------------------|
| Functionality | Patching |
| Application | Used in LSX-style frames only |
| Cable Exit Location | Upward |
| Cable Stub Type | IFC, stranded |
| Color | Putty white |
| Color, front | White |
| Growth Configuration | Fully loaded |
| Interface, front | SC/APC |
| Interface, rear | Stub tail |
| Rack Type | EIA 23 in |
| Rack Units | 8 |
| Shelf Movement | Fixed |
| Total Ports, quantity | 288 |

Dimensions

| | |
|---------------|------------------|
| Height | 279.4 mm 11 in |
| Width | 482.6 mm 19 in |
| Depth | 304.8 mm 12 in |

LSX-LL/OWB075

Cable Length 75 m | 246.063 ft

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

