# LSX-TL/OLH031



LSX Fiber Term Panel 6 Ru, 144 - SC/APC, Singlemode IFC Ribbon, 31 Meters, Far end connection Stub

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with IFC cable

**Product Series** LGX

### General Specifications

**Functionality** Patching

**Application** Used in LSX-style frames only

Cable Exit Location Upward

Cable Stub Type IFC, ribbon

**Color** Putty white

Color, front White

**Growth Configuration** Fully loaded

Interface, front SC/APC

Interface, rear Stub tail

Rack Type EIA 19 in | EIA 23 in

Rack Units 6

Shelf Movement Fixed

Total Ports, quantity 144

#### **Dimensions**

 Height
 228.6 mm | 9 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

 Cable Length
 31 m | 101.706 ft



# LSX-TL/OLH031

## Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

### Packaging and Weights

Packaging quantity

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

