## 760244560 | FACT-MMDLME-B



FACT® MPO Module, left sided, LC/APC at front side, 2x12 fiber MPO at rear side, singlemode, wiring method B Enhanced

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

#### **Product Classification**

Regional Availability Asia | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber module

Product Brand FACT®
Product Series FACT

## General Specifications

**Functionality** Breakout

**Application** For Use with FACT NG4 Universal Chassis

**Body Style** Left orientation

Color, bootBlackColor, housingBlackColor, rearGreenInterface, frontLC/APCInterface Feature, frontSimplexInterface Color, frontGreenInterface, rearMPO

Interface Feature, rear Female | Key up/up | Unpinned

Interface Color, rear Green

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 24

Total Ports, quantity, front 24

Total Ports, quantity, rear 2



# 760244560 | FACT-MMDLME-B

#### **Dimensions**

 Height
 13.21 mm | 0.52 in

 Width
 159.77 mm | 6.29 in

 Depth
 122.68 mm | 4.83 in

### Optical Specifications

Fiber ModeSinglemodeInsertion Loss, maximum0.75 dBInsertion Loss, typical0.6 dBReturn Loss, minimum62 dB

#### **Environmental Specifications**

Operating Temperature-5 °C to +40 °C (+23 °F to +104 °F)Storage Temperature-5 °C to +50 °C (+23 °F to +122 °F)

**Relative Humidity** Up to 85%, non-condensing

### Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

#### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

