

RCP-4KBPU009200



RapidFiber® Termination Panel, 288-Position 4RU, singlemode, LC/UPC to stub, 92m

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with rapid cable
Product Brand	RapidFiber®
Product Series	RCP

General Specifications

Functionality	Patching
Body Style	Symmetrical
Cable Exit Location	Rear, left side
Cable Stub Type	IFC, stranded
Color	Putty white
Door Type, front	Hinged Slide latch Transparent
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Interface, rear	Stub tail
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	4
Shelf Movement	Sliding
Total Fibers, quantity	288
Total Ports, quantity	288
Transmission Standards	IEC 60794-2 ISO/IEC 11801 TIA/EIA-568-B.3

Dimensions


Height	177.8 mm 7 in
---------------	-----------------

RCP-4KBPU009200

Width 482.6 mm | 19 in

Depth 381 mm | 15 in

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A2/B2

RCP-4KBPU009200

Environmental Specifications

Operating Temperature	-5 °C to +55 °C (+23 °F to +131 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–85%, non-condensing
Qualification Standards	NEBS Level 3 Telcordia GR-1435 Telcordia GR-326 Telcordia GR-409 UL 1863

Packaging and Weights

Packaging quantity	1
---------------------------	---

Included Products

760245201 P-024-MP-8V-F30YL	–	Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 24 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
--------------------------------	---	--