

RCP-4KBPUZ16039B



RapidFiber® Termination Panel, 288-Position 4RU, singlemode, LC/UPC to LC/APC breakouts, 160m cable with 39 inch breakout length and 1.2 MM Breakout Jacketing

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with rapid cable
Product Brand	RapidFiber®
Product Series	RCP

General Specifications

Functionality	Patching
Body Style	Symmetrical
Cable Exit Location	Rear, left side
Cable Stub Type	IFC, stranded
Color	Putty white
Door Type, front	Hinged Slide latch Transparent
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Interface, rear	LC/APC
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	4
Shelf Movement	Sliding
Total Fibers, quantity	288
Total Ports, quantity	288
Transmission Standards	IEC 60794-2 ISO/IEC 11801 TIA/EIA-568-B.3


Dimensions

Height	177.8 mm 7 in
---------------	-----------------

RCP-4KBPUZ16039B

Width	482.6 mm 19 in
Depth	381 mm 15 in
Breakout Length	39 in

Ordering Tree



ONLY FOR MULTIMODE VERSION.¹
 ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE²
 RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.³
 ONLY AVAILABLE IN LC288 4RU⁴

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D G.657.A2/B2

RCP-4KBPUZ16039B

Environmental Specifications

Operating Temperature	-5 °C to +55 °C (+23 °F to +131 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–85%, non-condensing
Qualification Standards	NEBS Level 3 Telcordia GR-1435 Telcordia GR-326 Telcordia GR-409 UL 1863

Packaging and Weights

Packaging quantity	1
---------------------------	---

Included Products

760245201 P-024-MP-8V-F30YL	–	Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 24 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
--------------------------------	---	--