FPM-07/K-AN010M

Fiber Optic Patch Cord, Multi-fiber, Singlemode, 4 fibers, SC/UPC to LC/UPC, yellow, 10 m

Product Classification

Regional AvailabilityLatin America| North AmericaProduct TypeFiber distribution cable assembly

Product Series FPM

General Specifications

Color, boot ABlueColor, boot BBlueColor, connector ABlueColor, connector BBlueConnector A, quantity4Connector B, quantity4

Construction Type Stranded
Interface, Connector A LC/UPC
Interface, Connector B SC/UPC
Jacket Color Yellow

Total Fibers, quantity

Dimensions

Cord Length 10 m | 32.808 ft

Optical Specifications

Fiber Mode Singlemode

Fiber TypeOS2Insertion Loss, maximum, connector A0.3 dBInsertion Loss, maximum, connector B0.2 dBReturn Loss, minimum, connector A55 dBReturn Loss, minimum, connector B55 dB

Environmental Specifications



FPM-07/K-AN010M

Environmental Space

Plenum

1

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

