

FPM-OK/O-M003M

Fiber Optic Pigtail, Multi-fiber, Singlemode, 12 fibers, LC/UPC to Stub, yellow, 3 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber pigtail, multi-fiber
Product Series	FPM

General Specifications

Connector A, quantity	12
Color, boot A	Blue
Color, connector A	Blue
Construction Type	Stranded
Interface, Connector A	LC/UPC
Jacket Color	Yellow
Total Fibers, quantity	12

Dimensions

Cord Length	3 m 9.843 ft
-------------	----------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2

Environmental Specifications

Environmental Space	Plenum
---------------------	--------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

FPM-OK/O-M003M

ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

