FPM-0K/0-M006.17M

Fiber Optic Pigtail, OS2, LC/UPC-stub, 12F soft wall, 900 #m buff. fiber, 12 " breakouts, 6.17 m, yellow

Product Classification

Regional Availability Latin America | North America

Product Type Fiber pigtail, multi-fiber

Product Series FPM

General Specifications

Color, boot A Blue
Color, connector A Blue

Construction Type Stranded
Interface, Connector A LC/UPC
Jacket Color Yellow
Total Fibers, quantity 12

Dimensions

Cord Length 6.17 m | 20.243 ft

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

COMMSCOPE®

FPM-0K/0-M006.17M

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

