FSWSASAW6



TeraSPEED® SC/APC to SC/APC, Distribution Cable, 6-Fiber, Plenum

Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®

Product Type Fiber distribution cable assembly
Product Brand SYSTIMAX InstaPATCH® 360

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters

General Specifications

Cable GlandsNo glandsColor, connector AGreenColor, connector BGreen

Construction Type Distribution, indoor

Interface, Connector ASC/APCInterface, Connector BSC/APC

Total Fibers, quantity 6


Dimensions

Cable Assembly Length Range (m)3-305Cable Assembly Length Range (ft)7-999

Ordering Tree



FSWSASAW6



Mechanical Specifications

Cable Retention Strength, maximum $0.50 \text{ lb} @ 0^{\circ} | 0.50 \text{ lb} @ 90^{\circ}$

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Plenum

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



460125859 - SC/APC Connector, Singlemode,

COMMSCOPE®



Green