

# NGFB-TB5SRUK

---



Next Generation Frame (NGF) Fiber Termination Block, LC/UPC, Adapter only, Right block

## Product Classification

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Regional Availability</b> | EMEA   Latin America   North America |
| <b>Product Type</b>          | Fiber patch block                    |
| <b>Product Series</b>        | NGFB                                 |

## General Specifications

|                              |                               |
|------------------------------|-------------------------------|
| <b>Functionality</b>         | Patching                      |
| <b>Application</b>           | Used in NGF-style frames only |
| <b>Body Style</b>            | Right orientation             |
| <b>Cable Exit Location</b>   | Upward                        |
| <b>Color</b>                 | Black                         |
| <b>Color, front</b>          | Black                         |
| <b>Door Type, front</b>      | Compression latch   Hinged    |
| <b>Growth Configuration</b>  | Fully loaded                  |
| <b>Interface, front</b>      | LC/UPC                        |
| <b>Rack Type</b>             | NGF                           |
| <b>Shelf Movement</b>        | Fixed                         |
| <b>Total Ports, quantity</b> | 288                           |

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

# NGFB-TB5SRUK

---

## Environmental Specifications

|                                |                                      |
|--------------------------------|--------------------------------------|
| <b>Operating Temperature</b>   | -5 °C to +50 °C (+23 °F to +122 °F)  |
| <b>Storage Temperature</b>     | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Relative Humidity</b>       | Up to 80%, non-condensing            |
| <b>Qualification Standards</b> | Telcordia GR-449-CORE                |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|