

FGS-HTBK-18-5-32PC



FiberGuide® 18in Horizontal Tool-less Bracket Kit for 4x12,4x18 and 4x24in Systems, 5in Tall, kit of 32

This 18in bracket attaches to 18in ladder rack using our tool-less Quick Knobs. Used to mount and support 4x12 and 4x18in FiberGuide® above ladder racking. Ships in a kit of 32 brackets.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Color	Black
Note	Includes fastening hardware
Orientation	Horizontal
Section Type	Bracket
Bracket Type	Center Support
Bracket Installation Type	N/A
Attachment Type	Ladder rack

Dimensions	
Height	171.501 mm 6.752 in
Width	114.3 mm 4.5 in
Length	460.096 mm 18.114 in
Thread Size	N/A
System Dimensions	102 mm x 305 mm (4 in x 12 in) 102 mm x 457 mm (4 in x 18 in) 102 mm x 610 mm (4 in x 24 in)

Packaging and Weights

Packaging quantity	32
---------------------------	----

FGS-HTBK-18-5-32PC

Weight, net

35.025 kg | 77.216 lb

Included Products

HDW-12021 – FiberGuide® Quick Knob with T-Bolt

HDW-12021



FiberGuide® Quick Knob with T-Bolt

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber raceway hardware
Product Brand	FiberGuide®
Product Series	FGS
Minimum Order Quantity	10

General Specifications

Color	Black
Orientation	Horizontal
Section Type	Accessory

Dimensions

System Dimensions	102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 102 mm x 305 mm (4 in x 12 in) 102 mm x 610 mm (4 in x 24 in) 51 mm x 152 mm (2 in x 6 in)
--------------------------	--

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Packaging quantity	1
Weight, net	0.015 kg 0.033 lb

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

HDW-12021

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

