

S-4-TCPUSEW-H-4316



Multiband Four-way Low PIM Reactive High Power Splitter, 340–3800 MHz (Additional mounting bracket PN:42396A-17 sold separately)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Power splitter

General Specifications

Device Type	Splitter
Application	Indoor/Outdoor
Color	White
Inner Contact Plating	Silver
Interface	4.3-10 Female
Outer Contact Plating	Trimetal

Dimensions

Height	25 mm 0.984 in
Width	66 mm 2.598 in
Length	352 mm 13.858 in

Electrical Specifications

3rd Order IMD	-165 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss at Frequency Band	0.4 dB @ 340–2700 MHz 0.6 dB @ 2700–3800 MHz
Average Power, maximum	300 W
Impedance	50 ohm
Operating Frequency Band	340 – 3800 MHz
Peak Power, maximum	3 kW
Power Rating, Splitting	300 W
Reflected Power, maximum	300 W
Split Loss	6 dB

S-4-TCPUSEW-H-4316

VSWR at Frequency Band 1.25:1 @ 340–3800 MHz

Environmental Specifications

Operating Temperature -25 °C to +85 °C (-13 °F to +185 °F)

Relative Humidity Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP65

Packaging and Weights

Height, packed 55 mm | 2.165 in

Width, packed 77 mm | 3.031 in

Length, packed 380 mm | 14.961 in

Weight, gross 0.722 kg | 1.592 lb

Weight, net 0.646 kg | 1.424 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

